


# Adjustable Clamping Lever

threaded bore - stainless



# 74380



## Material

Stainless steel, 1.4308 (AISI CF-8).  
Matte blasted.  
Inner parts: stainless, 1.4305.  
Screw & spring: stainless, 1.4300.


## Technical Notes

By lifting the lever, the serrations are disengaged. The handle can be positioned by the serrations, and the threaded insert can be exchanged. Upon releasing the handle, the serrations are automatically re-engaged.

## Tips

Ideal for applications with aggressive environments, such as food processing, chemical industries etc.



Order No.	$l_1$	$d_1$	$d_3$	$d_4$	$h_1$	$h_2$	$h_3$	Stroke $s_1$	$t$ min.	 g
74380.W0111	45	M 5	10,0	13,0	24,5	4,0	35	3,5	9	37
74380.W0121	45	M 6	10,0	13,0	24,5	4,0	35	3,5	9	30
74380.W0311	63	M 6	13,5	17,5	31,0	6,5	45	4,0	11	80
74380.W0321	63	M 8	13,5	17,5	31,0	6,5	45	4,0	11	50
74380.W0411	78	M 8	16,0	21,0	36,0	8,0	55	4,0	14	140
74380.W0421	78	M10	16,0	21,0	36,0	8,0	55	4,0	14	140