




# Free Running Safety Clamping Lever, free-running when not engaged

## Clamping Levers



74860

CLAMPING LEVERS

### Material

Plastic technopolymer (polyamide PA)  
glass fibre reinforced, black.  
Inner parts: steel, blackened embedded in  
black plastic.

### Tips

Unique Safety Handle.

When not in use, the lever is not engaged  
with threaded insert, i.e. the adjustable  
lever turns freely.

As soon as the lever hub is pushed down,  
both serrations will engage, allowing the  
fixture to be released or clamped.

After „releasing“, the lever disengages

through spring tension.

### Important Notes

Used where accidental loosening or read-  
justment can result in accidents.  
Temperature resistant to +130°C.

Order No.	$l_1$	$d_1$	$d_2$	$d_3$	$h_1$	$h_2$	$h_3$	$h_4$ stroke	t min.	Weight g
74860.W0041	44	M 4	12	15.5	29	9	36	3.5	10	14
74860.W0042	44	M 5	12	15.5	29	9	36	3.5	10	13
74860.W0043	44	M 6	12	15.5	29	9	36	3.5	10	12
74860.W0061	63	M 6	15	19.0	37	12	48	4.0	13	25
74860.W0062	63	M 8	15	19.0	37	12	48	4.0	13	24