


Safety Lever Toggle Clamps



Material

Body: steel, zinc plated. Rivets: stainless steel running in hardened bushes. Pre-lubricated bearings (grease suitable for food industry use). Handle: ergonomic soft feel, oil-resistant with a large grip area.

Technical Notes

The safety knob holds the clamp in both the open and the closed position. This prevents opening under vibration or inadvertent movement of the clamping arm when loading or unloading a fixture. Without angle bracket. Push and pullclamping (equal operation of rod and lever). Long rod-guide with attaching thread and nut. Temperature range -10°C to +80°C.

Order No.	Size	F ₁ kN	F ₂ kN	Clamping screw	d_1	d ₂	h_1	h ₂	I_1	l ₂	l ₃ min. max.	I ₄	I_5	I ₆	w_1	w ₂	Weight
41895.W0003																	





Toggle Clamps

Wixroyd Toggle Clamps





Welding Fixtures






Machining and Jig Assemblies





Cmm's







wixroyd.com



Wixroyd Toggle Clamps

overview

Toggle Clamps







Mounting Base Variations

Clamping Variations

Horizontal base

Vertical base

Angled base





Horizontal acting



Push-pull



Latch type


Hook type

Explanation of forces

The force transmitted to the workpiece by the toggle clamp's closed arm, without itself being deformed when machine forces are applied. The holding force value is dependent upon the proximity of the measuring load point to the toggle clamp's pivot point (therefore two values, F1 and F2 are provided).


The force applied to the workpiece when the toggle clamp's arm is closed. These clamping forces can only be stated for pneumatic toggle clamps, clamping forces of manual clamps cannot be easily measured as they are dependent upon the operator.

For pneumatically controlled toggle clamps only, F5 is the piston force required (at 6 bar to) achieve the stated clamping force.



Holding Forces F1 or F2





Piston Forces F5



sales@wixroyd.com

Toggle Clamps

Wixroyd Toggle Clamps

overview



Quality Features



Ergonomic soft grip 2-component handle



Stainless rivets and hardened bushings



Moveable stop for variable opening angle



Operator finger protection



Temperature resistant


Unique Features



Safety catches



Heavy duty versions



Pneumatic versions



Matt black surface for optical measurement

Materials



Steel, zinc plated and passivated



Stainless steel (304)



Steel, matt black vario-spektron coated



Protective cap and handle made of an electrostatic conductive (dissipative) material.



