




79360

PULL HANDLES

Material

Connection shank: die-cast aluminium, black powder coated, semi-matte.
Connection tube: die-cast aluminium, anodised, natural, satin finish. RAL 7043.

Technical Notes

Supplied with hex screw DIN 912, M12x70

with suitable nuts and washers.
Minimum stress resistance >1000N.

Tips

Machine, instrument and equipment handles for universal use and for any hole spacing.
Extra rugged design. Handle ledge and

elbow section plug press-connected.

Order No.	l_1	l_2	l_3	a_1	b_1	d_1	h_1	w_1	w_2
79360.W0180	180	208	100	20	28	M 12	60	34	40
79360.W0200	200	228	220	20	28	M 12	60	34	40
79360.W0250	250	278	170	20	28	M 12	60	34	40
79360.W0300	300	328	220	20	28	M 12	60	34	40
79360.W0350	350	378	270	20	28	M 12	60	34	40
79360.W0400	400	428	320	20	28	M 12	60	34	40
79360.W0500	500	528	420	20	28	M 12	60	34	40
79360.W0600	600	628	520	20	28	M 12	60	34	40