




Combination Toggle Clamp

position and clamp

Auto-Adjust Toggle Clamps



42500

AUTO-ADJUST TOGGLE CLAMPS

Material

Body: steel, zinc plated.
 Rivets: stainless steel running in hardened bushes. Pre-lubricated bearings (grease suitable for food industry use).

Ergonomic, soft feel and oil-resistant handle with large grip area.

Technical Notes

Especially useful in welding applications.

The positioning rod and toggle clamp achieve precise positioning and clamping of components in one operation.
 Temperature range -10°C to +80°C.

Order No.	Size	F ₁ kN	F ₂ kN	d ₁	h ₁	h ₂	h ₃	h ₄ min.	h ₄ max.	h ₅	h ₆	l ₁	Weight g
42500.W0001	1	1.0	1.0	5.5	74	62	36.0	25	32	22	12	150	340
42500.W0002	2	2.0	2.0	6.5	94	87	46.0	30	40	28	16	219	700
42500.W0003	3	3.0	3.0	8.5	110	106	55.5	40	50	34	20	270	1620

Order No.	l ₂	l ₃	l ₄	l ₅	l ₆ min.	l ₆ max.	l ₇	l ₈	w ₁	w ₂	w ₃
42500.W0001	55	40	33	15	5	10	7.5	0.5	53	34,5-39,5	17.0
42500.W0002	75	50	56	32	14	24	12.5	9.0	75	48,5-61,5	19.5
42500.W0003	90	50	74	37	20	30	20.0	14.0	96	60,0-80,0	29.0

