




# Compression Latch - Flexi System

insert driver - fixed grip - zinc



## Compression Latches



**A1580**

COMPRESSION LATCHES

### Material

Body: die cast zinc, bright chrome plated.  
Insert: steel.

**Not supplied:** KEY - order separately.

### Technical Notes

**Order key separately.**

**Keys:** see A0102.AW0060.

Insert driver compression latch enabling tight securing of enclosure door. Via welding a fastening nut (M 8) to the enclosure frame the fastening stud can be engaged and turned until the enclosure door is adequately tightened and secured (use triangle 7 key A0102.AW0060 to activate driver).

vate driver).

### Tips

Security cover type can be secured with wire or cable tie for tamper evident security.

h = grip length.

Order No.	Insert type	Lock type	a	b	lh	l <sub>1</sub>	l <sub>2</sub>	h
<b>A1580.AW0023</b>	Triangle 7	W/o Security Cover	28	4	18	40	2.5	23
<b>A1580.AW0028</b>	Triangle 7	W/o Security Cover	28	4	18	46	7.5	28
<b>A1580.AW0034</b>	Triangle 7	W/o Security Cover	28	4	18	54	13.5	34
<b>A1580.AW0223</b>	Triangle 7	With Security Cover	29	13	18	40	2.5	23
<b>A1580.AW0228</b>	Triangle 7	With Security Cover	29	13	18	46	7.5	28
<b>A1580.AW0234</b>	Triangle 7	With Security Cover	29	13	18	54	13.5	34

