




Anti-vibration Cylinders Waisted

male:female

Anti-Vibration



61110

ANTI-VIBRATION

Material

Rubber on silver zinc plated steel (rubber hardness - 55 Shore A).

Tips

These cylinders are used to reduce vibra-

tion by allowing some movement (in axial and radial as shown).


Typically used in machinery, compressors, air conditioning units, light engineering equipment etc.

Order No.	d ₁	h ₁	d ₂	l ₁	d ₃	Compression max.	Axial load kgf max.	Radial load kgf max.
61110.W0200	20	20	M 6	18	12	2.5	15	3.0
61110.W0250	30	25	M 8	20	24	4	40	4.0
61110.W0400	40	28	M10	25	22	5	60	2.5
61110.W0600	60	36	M10	30	37	5	90	7.0
61110.W0601	60	43	M10	30	35	4	70	12.0
61110.W0602	60	60	M10	30	51	6	150	30.0
61110.W0700	70	56	M12	35	50	6	220	45.0
61110.W0800	80	65	M12	35	70	8	400	55.0
61110.W0900	90	50	M12	45	80	4	800	65.0
61110.W1300	130	96	M16	45	115	13	1400	70.0




Acceptable loads

Cylindrical mounts are never to be used in tension, they should only be used in axial or radial. Radial loads are however considerably less than axial loads. Parts with small diameters (d_1) and relatively long lengths (h) cannot accept radial loads.



Installation

Incorrect installation



Correct installation

The height of the insulator may vary as the rubber is compressed under load.

Do not remove the rubber burr around the edge of the metal, this could cause detachment of rubber from the metal studs.

