


Cam Locks - Flexi-System fixed grip - zinc







A2001

Material

Type one & Two: Body: die cast zinc, finished in chrome plate or black powder coating.

Cylinder lock: die cast zinc, chrome plated. **Type Three:** Body: polyamide.

Cylinder lock: die cast zinc, chrome plated. **Supplied with:** Keys: two per lock. **Not supplied:** CAM - order separately.

Technical Notes

Order cam separately.

Cams: see suitable cam A0203, A0224 and A0240. Select "without projection" cam type.

Dimensions ch and cl relate to cam. Use formula to calculate ch (required cam offset), and refer to cam selection chart; **ch = h - lh** where;

ch = required cam off-set/height.

h = grip length (distance between inside of latch face and front of cam).

lh = body length of cam latch/lock to be

used (see product table below).

Rods & Guides: to achieve 3-point latching - A0303, A0321, A0325.

Tips

Quarter turn opening or closing. Universal left and right application.

Important Notes

Sold subject to pack quantity.

Order No.	Туре	Body finish	Key type	d_1	h_1	lh
A2001.AW0010	One	Chrome Plated	Keyed Alike	28.0	6	20
A2001.AW0310	Two	Black Coated	Keyed Alike	28.0	6	18
A2001.AW0320	Two	Black Coated	Keyed to Differ	28.0	6	18
A2001.AW0330	Two	Black Coated	Euro	30.0	6	18
A2001.AW0510	Three	Plastic, Black	Keyed Alike	28.0	6	18
A2001.AW0520	Three	Plastic, Black	Keyed to Differ	28.0	6	18

