



61350

ANTI-VIBRATION

Material

Rubber on zinc plated steel.

Order No.	Type	d ₁	l ₁	d ₂	d ₃	h ₁	Compression max.	Static load kgf max.
61350.W0105	Type 1	50	-	10.5	-	15	2.2	180
61350.W0108	Type 1	85	-	10.5	-	15	1.6	450
61350.W0205	Type 2	55	25	M12	-	16	2.2	180
61350.W0208	Type 2	85	25	M12	-	16	1.6	450
61350.W0212	Type 2	125	25	M12	-	16	2.2	800
61350.W0305	Type 3	50	-	6.0	45	18	2	50
61350.W0309	Type 3	91	-	6.5	86	18	2	350
61350.W0313	Type 3	138	-	10.5	130	25	2.6	900



Recommendations for machine mounts

Machine mounts should be installed between two parallel and perfectly flat surfaces. Mounts operating tilted or twisted do not work properly. This may be due to incorrect alignment, tolerances in the building of the structure or over-tightened torque during the installation of the anti-vibration mounts.

ANTI-VIBRATION

