

### 61460

ANTI-VIBRATION

#### Material


Rubber on silver zinc plated steel (rubber hardness - 55 Shore A).

#### Technical Notes

Used to support machine tools and packaging machinery.

Provides vibration isolation for frequencies higher than 20Hz.

Order No.	Type	$d_1$	$l_1$	$h_1$	$l_2$	$l_3$	$l_4$	$w_1$	Axial load kgf max.	Compression max.
61460.W0105	Type 1	M12	50	20	37	-	-	60	250	2
61460.W0110	Type 1	M12	100	20	37	-	-	60	500	2
61460.W0115	Type 1	M12	150	20	37	-	-	60	750	2
61460.W0120	Type 1	M12	200	20	37	-	-	60	1000	2
61460.W0205	Type 2	M12	50	23	37	85	115	60	250	2
61460.W0210	Type 2	M12	100	23	37	135	165	60	500	2
61460.W0215	Type 2	M12	150	23	37	185	215	60	750	2
61460.W0220	Type 2	M12	200	23	37	235	265	60	1000	2



### Recommendations for machine mounts

Machine mounts should be installed between two parallel and perfectly flat surfaces. Mounts operating tilted or twisted do not work properly. This may be due to incorrect alignment, tolerances in the building of the structure or over-tightened torque during the installation of the anti-vibration mounts.

ANTI-VIBRATION

