




74200

CLAMPING LEVERS

Material

Steel, blackened.

Order No.	Finish	a	b ≈	d ₁	d ₂ tol. H7	d ₂	d ₃	h ≈	l ₁	l ₂ ≈	Weight g
74200.W0105	Smooth Bore	4.0	9.5	8	6	-	12	24.0	50	48	16
74200.W0106	Smooth Bore	5.0	12.0	10	8	-	16	30.5	63	60	37
74200.W0108	Smooth Bore	6.0	14.5	13	10	-	20	38.0	80	76	73
74200.W0110	Smooth Bore	7.5	18.5	16	12	-	25	47.0	100	95	140
74200.W0112	Smooth Bore	10.0	24.0	20	16	-	32	59.5	125	119	282
74200.W0116	Smooth Bore	12.5	30.0	25	20	-	40	75.7	160	152	553
74200.W0120	Smooth Bore	18.0	40.0	32	24	-	50	97.0	200	190	1096
74200.W0305	Threaded Bore	4.0	9.5	8	-	M 6	12	24.0	50	48	17
74200.W0306	Threaded Bore	5.0	12.5	10	-	M 8	16	30.5	63	60	38
74200.W0308	Threaded Bore	6.0	15.0	13	-	M10	20	38.0	80	76	74
74200.W0310	Threaded Bore	7.5	19.0	16	-	M12	25	47.0	100	95	142
74200.W0312	Threaded Bore	10.0	25.0	20	-	M16	32	59.5	125	119	297
74200.W0316	Threaded Bore	12.5	31.0	25	-	M20	40	75.7	160	152	566
74200.W0320	Threaded Bore	18.0	41.0	32	-	M24	50	97.0	200	190	1140