




# Adjustable Clamping Lever

threaded bore - stainless

## Clamping Levers



**74380**

CLAMPING LEVERS

### Material

Stainless steel, 1.4308 (AISI CF-8). Matte blasted.

Inner parts: stainless, 1.4305.

Screw & spring: stainless, 1.4300.

disengaged. The handle can be positioned by the serrations, and the threaded insert can be exchanged. Upon releasing the handle, the serrations are automatically re-engaged.

ronments, such as food processing, chemical industries etc.

### Technical Notes

By lifting the lever, the serrations are

### Tips

Ideal for applications with aggressive envi-

Order No.	$l_1$	$d_1$	$d_3$	$d_4$	$h_1$	$h_2$	$h_3$	$t$ min.	Stroke $s_1$	Weight g
74380.W0111	45	M 5	10.0	13.0	24.5	4.0	35	9	3.5	37
74380.W0121	45	M 6	10.0	13.0	24.5	4.0	35	9	3.5	30
74380.W0311	63	M 6	13.5	17.5	31.0	6.5	45	11	4.0	80
74380.W0321	63	M 8	13.5	17.5	31.0	6.5	45	11	4.0	50
74380.W0411	78	M 8	16.0	21.0	36.0	8.0	55	14	4.0	140
74380.W0421	78	M10	16.0	21.0	36.0	8.0	55	14	4.0	140