


Gear Lever Handles

steel or stainless steel

Clamping Levers



74600

CLAMPING LEVERS

Material

Shafts: steel, galvanized, passivated or stainless steel 1.4305 (AISI 303) - matt

finish.

Temperature range 110°C.
Knobs: plastic, duroplast PF 31.

Technical Notes

Temperature range up to 110°C

Order No.	Type	d ₁	d ₂	d ₃	l ₁	l ₂	l ₃	Weight g
74600.W0020	Steel Shaft - Ball	8	M 6	20	63	9	18.0	30
74600.W0022	Steel Shaft - Ball	8	M 6	20	100	9	18.0	39
74600.W0025	Steel Shaft - Ball	10	M 8	25	80	11	22.5	50
74600.W0026	Steel Shaft - Ball	10	M 8	25	100	11	22.5	62
74600.W0027	Steel Shaft - Ball	10	M 8	25	125	11	22.5	76
74600.W0032	Steel Shaft - Ball	12	M10	32	100	14	29.0	96
74600.W0033	Steel Shaft - Ball	12	M10	32	125	14	29.0	118
74600.W0034	Steel Shaft - Ball	12	M10	32	160	14	29.0	146
74600.W0035	Steel Shaft - Ball	14	M12	35	125	16	32.5	157
74600.W0036	Steel Shaft - Ball	14	M12	35	160	16	32.5	203
74600.W0037	Steel Shaft - Ball	14	M12	35	200	16	32.5	251
74600.W0040	Steel Shaft - Ball	16	M14	40	160	18	37.0	310
74600.W0041	Steel Shaft - Ball	16	M14	40	200	18	37.0	326
74600.W0042	Steel Shaft - Ball	16	M14	40	250	18	37.0	397
74600.W0520	Stainless Shaft - Ball	8	M 6	20	63	9	18.0	30
74600.W0522	Stainless Shaft - Ball	8	M 6	20	100	9	18.0	44
74600.W0525	Stainless Shaft - Ball	10	M 8	25	80	11	22.5	55
74600.W0526	Stainless Shaft - Ball	10	M 8	25	100	11	22.5	63
74600.W0527	Stainless Shaft - Ball	10	M 8	25	125	11	22.5	78
74600.W0530	Stainless Shaft - Ball	12	M10	32	100	14	29.0	97
74600.W0531	Stainless Shaft - Ball	12	M10	32	125	14	29.0	120
74600.W0532	Stainless Shaft - Ball	12	M10	32	160	14	29.0	154
74600.W0535	Stainless Shaft - Ball	14	M12	35	125	16	32.5	159
74600.W0536	Stainless Shaft - Ball	14	M12	35	160	16	32.5	202
74600.W0537	Stainless Shaft - Ball	14	M12	35	200	16	32.5	250
74600.W0120	Steel Shaft - Taper	8	M 6	18	63	9	40.0	26
74600.W0122	Steel Shaft - Taper	8	M 6	18	100	9	40.0	42
74600.W0125	Steel Shaft - Taper	10	M 8	21	80	11	50.0	50
74600.W0126	Steel Shaft - Taper	10	M 8	21	100	11	50.0	62
74600.W0127	Steel Shaft - Taper	10	M 8	21	125	11	50.0	78
74600.W0130	Steel Shaft - Taper	12	M10	23	100	14	65.0	81
74600.W0131	Steel Shaft - Taper	12	M10	23	125	14	65.0	103
74600.W0132	Steel Shaft - Taper	12	M10	23	160	14	65.0	133
74600.W0135	Steel Shaft - Taper	14	M12	26	125	16	80.0	125



Order No.	Type	d ₁	d ₂	d ₃	l ₁	l ₂	l ₃	Weight g
74600.W0136	Steel Shaft - Taper	14	M12	26	160	16	80.0	168
74600.W0137	Steel Shaft - Taper	14	M12	26	200	16	80.0	216
74600.W0140	Steel Shaft - Taper	16	M14	28	160	18	90.0	214
74600.W0141	Steel Shaft - Taper	16	M14	28	200	18	90.0	273
74600.W0142	Steel Shaft - Taper	16	M14	28	250	18	90.0	352
74600.W0620	Stainless Shaft - Taper	8	M 6	18	63	9	40.0	27
74600.W0622	Stainless Shaft - Taper	8	M 6	18	80	9	40.0	33
74600.W0624	Stainless Shaft - Taper	8	M 6	18	100	9	40.0	41
74600.W0630	Stainless Shaft - Taper	10	M 8	21	80	11	50.0	50
74600.W0632	Stainless Shaft - Taper	10	M 8	21	100	11	50.0	62
74600.W0634	Stainless Shaft - Taper	10	M 8	21	125	11	50.0	78
74600.W0640	Stainless Shaft - Taper	12	M10	23	100	14	65.0	81
74600.W0642	Stainless Shaft - Taper	12	M10	23	125	14	65.0	103
74600.W0644	Stainless Shaft - Taper	12	M10	23	160	14	65.0	133
74600.W0650	Stainless Shaft - Taper	14	M12	26	125	16	80.0	125
74600.W0652	Stainless Shaft - Taper	14	M12	26	160	16	80.0	168
74600.W0654	Stainless Shaft - Taper	14	M12	26	200	16	80.0	216