




Free Running Safety Clamping Lever, free-running when not engaged

Clamping Levers



74880

CLAMPING LEVERS

Material

Plastic technopolymer (polyamide PA)
glass fibre reinforced, black.
Inner parts: steel, blackened embedded in
black plastic.

Tips

Unique Safety Handle.

When not in use, the lever is not engaged
with threaded insert, i.e. the adjustable
lever turns freely.

As soon as the lever hub is pushed down,
both serrations will engage, allowing the
fixture to be released or clamped.

After „releasing“, the lever disengages

through spring tension.

Important Notes

Used where accidental loosening or read-
justment can result in accidents.
Temperature resistant to +130°C.

Order No.	l_1	d_1	d_2	d_3	h_1	h_2	h_3	h_4 stroke	l_2	Weight g
74880.W0061	44	M 6	12	15.5	29	9	36	3.5	16	18
74880.W0062	44	M 6	12	15.5	29	9	36	3.5	25	21
74880.W0081	63	M 8	15	19.0	37	12	48	4.0	20	38
74880.W0082	63	M 8	15	19.0	37	12	48	4.0	30	43