





Cam Locks - Flexi-System

fixed grip - zinc



A2001

CAM LOCKS

Material

Type one & Two: Body: die cast zinc, finished in chrome plate or black powder coating.
Cylinder lock: die cast zinc, chrome plated.
Type Three: Body: polyamide.
Cylinder lock: die cast zinc, chrome plated.
Supplied with: Keys: two per lock.
Not supplied: CAM - order separately.

Technical Notes

Order cam separately.

Cams: see suitable cam A0203, A0224 and A0240. Select „without projection“ cam type.

Dimensions ch and cl relate to cam. Use formula to calculate ch (required cam off-set), and refer to cam selection chart;

ch = h - lh where;

ch = required cam off-set/height.

h = grip length (distance between inside of latch face and front of cam).

lh = body length of cam latch/lock to be

used (see product table below).

Rods & Guides: to achieve 3-point latching - A0303, A0321, A0325.

Tips

Quarter turn opening or closing.
Universal left and right application.

Important Notes

Sold subject to pack quantity.

| Order No. | Type | Body finish | Key type | d ₁ | h ₁ | lh |
|--------------|-------|----------------|-----------------|----------------|----------------|----|
| A2001.AW0010 | One | Chrome Plated | Keyed Alike | 28.0 | 6 | 20 |
| A2001.AW0310 | Two | Black Coated | Keyed Alike | 28.0 | 6 | 18 |
| A2001.AW0320 | Two | Black Coated | Keyed to Differ | 28.0 | 6 | 18 |
| A2001.AW0330 | Two | Black Coated | Euro | 30.0 | 6 | 18 |
| A2001.AW0510 | Three | Plastic, Black | Keyed Alike | 28.0 | 6 | 18 |
| A2001.AW0520 | Three | Plastic, Black | Keyed to Differ | 28.0 | 6 | 18 |