


## Swing Handles - Cam Control

### 40mm euro cylinder - sliding cover - polyamide

## Swing Handles



#### Material

**Technical Notes** 

Body & Handle: die cast zinc, black powder coated.

Cylinder lock: die cast zinc, chrome plated. Supplied with: Keys: two per lock. Not supplied: Cam: order separately. **Cams:** see suitable cam A0203, A0224 and A0240. Select "without projection" cam type.

Dimensions ch and cl relate to cam. Use formula to calculate ch (required cam offset), and refer to cam selection chart; ch = h - lh where;

**ch** = required cam off-set/height.

h = grip length (distance between inside of latch face and front of cam). lh = body length of cam latch/lock to be used (see product table below). Rods & Guides: to achieve 3-point latching - A0303, A0321, A0325.

# Order cam separately.

Order No.	Finish	Lock type	Key type	I.	W	lh
B1450.AW0010	Black Coated	40 Euro	Keyed Alike	215.5	36	20

