


Retractable Clamps with adjustable handle

Adjustable Vertical Clamps



12610.1

ADJUSTABLE VERTICAL CLAMPS

Material

Body/spindle: steel (C45), tempered and black oxide finish.

Arm/joint: steel (35CrMo), tempered and

black oxide finish.

Tips

Clamping height can be adjusted. The


values in brackets shows clamping height range. Screw clamping mechanism allows for longer clamping stroke and greater clamping force.


Order No.	h_1	h_2	h_3	h_4	h_5	h_6	l_1	l_2	l_3	l_4	Weight g
12610.W0006	81	45	10	24.0	8	47	18	25.5	20	25	242
12610.W0008	100	55	12	30.5	10	63	22	32.0	25	31	490

Order No.	l_5	l_6	r_1	w_1	w_2	w_3	w_4	w_5	d_1	Handle load N max.	Clamping height finished surface min.	Clamping height finished surface max.	Clamping height rough surface min.	Clamping height rough surface max.	Clamping stroke s_1	Clamping force kN max.	Clamping mechanism
12610.W0006	16	11	40	42	26	22	32	M 6x1	5.5	170	32 (32,0~29,5)	40 (40,0~37,5)	35 (35,0~32,5)	43 (43,0~40,5)	2.5	2.4	Screw
12610.W0008	20	14	65	52	32	28	40	M 8x1,25	6.5	210	37 (37,0~33,5)	48 (48,0~44,5)	42 (42~38,5)	53 (53,0~49,5)	3.5	4.2	Screw

Adjustable Vertical Clamps


Retractable Clamps with adjustable handle





Retractable Clamps with eccentric handle

Adjustable Vertical Clamps



12610.2

ADJUSTABLE VERTICAL CLAMPS

Material

Body/spindle: steel (C45), tempered and black oxide finish.

Arm/joint: steel (35CrMo), tempered and

black oxide finish.

Tips

Clamping height can be adjusted. The

values in brackets shows clamping height range.

Order No.	h_1	h_2	h_3	h_4	h_5	h_6	l_1	l_2	l_3	l_4	Weight g
12610.W0106	89	45	10	24.0	8	50	18	25.5	20	25	244
12610.W0108	109	55	12	30.5	10	63	22	32.0	25	31	468

Order No.	l_5	l_6	w_1	w_2	w_3	w_4	w_5	d_1	Handle load N max.	Clamping height finished surface min.	Clamping height finished surface max.	Clamping height rough surface min.	Clamping height rough surface max.	Clamping stroke s_1	Clamping force kN max.	Clamping mechanism	Overall stroke s_2
12610.W0106	16	11	42	26	22	32	M 6x1	5.5	100	32 (31,5~32,5)	40 (39,5~40,5)	35 (34,5~35,5)	43 (42,5~43,5)	1.0	0.7	Spiral Cam, 4°	1.5
12610.W0108	20	14	52	32	28	40	M 8x1, 25	6.5	150	37 (36,4~37,6)	48 (47,4~48,6)	42 (41,4~42,6)	53 (52,4~53,6)	1.2	1.1	Spiral Cam, 4°	1.8

Adjustable Vertical Clamps

Retractable Clamps with eccentric handle

