


Drawer Slide - Full Extension

60 Kg load per pair

Full Extension



Material

Cold rolled steel, zinc plated.

Technical Notes

Hold-in detent when slide closed. Positive stop. Rails can be disconnected via pres-

sing disconnect lever.


These slides have been tested to 80,000 usage cycles.

centre of the rails using all mounting holes. Sold individually as single slides.

Important Notes

Load capacity is static load per pair, at the

Order No.	Slide length sl	Slide travel tr ±3.0	b	С	d	е	f	g	h	Load/pair kg max.	Weight g
P2200.AC0304	304.8	304.8	-	-	-	-	-	96.0	128.0	60	740
P2200.AC0355	335.6	335.6	-	-	-	-	46.6	128.0	128.0	60	860
P2200.AC0406	406.4	406.4	288.0	-	-	-	33.4	160.0	160.0	60	985
P2200.AC0457	457.2	457.2	352.0	-	25.45	32.15	-	160.0	192.0	60	1110
P2200.AC0508	508.0	508.0	352.0	416.0	25.45	32.15	-	192.0	224.0	60	1250
P2200.AC0558	558.8	558.8	352.0	416.0	25.45	32.15	57.8	224.0	256.0	60	1380
P2200.AC0609	609.6	609.6	352.0	480.0	25.45	32.15	44.8	256.0	256.0	60	1500
P2200.AC0660	660.4	660.4	352.0	544.0	25.45	32.15	-	256.0	320.0	60	1620
P2200.AC0711	711.2	711.2	352.0	544.0	25.45	32.15	82.2	256.0	352.0	60	1750





P2000 - P7200 Drawer Slides

Drawer Slides technical information



Weight capacity	Weight capacity/pair Kg - is the static load per pair of drawer slides, measured at the centre of a pair of slides, side mounted, spaced 450mm apart, and is based on use of all fixing points on the slide.								
	Important Note: Flat mounting of drawer slides, as opposed to the standard side mounding of slides, is not recommended as it results in a greatly reduced load capacity equal to only 25% of the stated weight capacity.								
Drawer slide terms	Slide length (sl) The longest dimension of a fully closed slide, this should not exceed the depth of cabinet in which slide is installed.								
	Slide travel (tr)	r) Distance a drawer slide moves from fully closed position. (slide length + slide travel = fully extended slide length).							
		b	75%						
	Full extension This type of drawer slide can be extended 100% of slide length, this is standard for most 3 piece drawer slides.								
	3/4 extension	ion This type of drawer slide extends to approx. 75% of the slide length, this is standard for most 2 piece drawer slides.							
	Positive stop	Drawer stops at extended/open posit	ion but does not lock or detent.						
	Positive lock	Drawer is firmly held in extended/open position by means of a mechanical catch. Drawer is released by depressing a lever and pushing drawer inward. From the extended/ open position the same slide may be disconnected by depressing the lever and pulling the drawer out.							
	Hold-in detent	 nt Drawer is firmly held in closed position, and released by pulling drawer open (also known as positive catch). nect From the extended/open position the slide may be disconnected by depressing lever and pulling drawer out. 							
	Lever disconnect								
	Self-closing	Toward end of drawer slide closing stroke, slide is drawn into the fully closed position.							
	Soft self-closing	Toward end of drawer slide closing st drawn into fully closed position.	roke, slide movement is slowed and then						
Side mounting tolerances		e recommend a side space equal to s with an additional 0,2 to 0,5 mm oning.	side space						
	can result in poor	s than 0,2 mm side tolerance running of the drawer slide and de - the same is true if tolerances sed.	side space = nominal slide thickness +0.2 to +0.5mm						
		nclosure faces are square and nounting of the drawer slides.	slide thickness						



wixroyd.com



Wixroyd Drawer Slides

Drawer Slides

product selection charts

