





End Mount Concealed Pivot Hinge

spring loaded - screw or weld-on - steel



Hinges



S2205

HINGES

Material

Body: steel, zinc plated.

Technical Notes

For sheet metal doors, cabinets and machinery covers. Spring body can be either welded, or screw mounted.

Pull back pin lever, hinge pin is retracted.
Release pin lever and hinge pin springs back.
Max. opening angle 110°.

Tips

Spring loaded feature of hinge enables

easy assembly and disassembly of panel/door, ideal for maintenance covers.
Typical assembly utilises spring loaded hinge at top of door and corresponding hinge spigot at foot of door.

Order No.	Hand	l_1	w_1	d_1	d_2	F_x N	F_y N	l_2	l_3	l_4	w_2	w_3	ts
S2205.AW0032	Left	52	16.5	4	3.2	150	200	32.0	19	10	5	8.5	2
S2205.AW0132	Right	52	16.5	4	3.2	100	130	32.0	19	10	5	8.5	2
S2205.AW0063	Left	89	26.5	6	5.5	150	200	62.5	45	15	6	15.2	2
S2205.AW0163	Right	89	26.5	6	5.5	150	200	62.5	45	15	6	15.2	2

