




Push Knobs no latch

Catches & Latches



E0300

CATCHES & LATCHES

Material

Push knob: zinc alloy, plated gold or chrome.

Body: ABS plastic, black.

35mm.

When installed push knob is near flush with surface, raised only 4mm.

Supplied with screws (M 3x20).

bore is required.

For surfaces 26 to 35mm thick, 40mm dia. counter bore of depth „h“ is required.

h = door thickness - 25mm.

Technical Notes

Suitable for door/wall thicknesses 15 to

Tips

For surfaces 15 to 25mm thick no counter

| Order No. | Finish | Weight g |
|--------------|--------|-------------|
| E0300.AC0030 | Gold | 67 |
| E0300.AC0040 | Chrome | 67 |




Gold



Chrome



E0800



Material

Push knob: zinc alloy.
Body and catch plate: ABS plastic, black.

Technical Notes

Suitable for door/wall thicknesses 15 to 30mm. For 13mm door use a 2mm plastic spacer (order separately).
When installed the push knob is near flush, raised only 4mm from surface.
Supplied with screws (M 3.1x10 and M

3.1x28), and catch plate.

Tips

To operate the push knob:

- Step 1:** door closed, latch is engaged.
- Step 2:** depress knob to flush position to lock.
- Step 3:** depress knob to the out position to unlock latch.


For surfaces between 15 to 25mm thick no

counter bore is required.
For surfaces from 26 to 35mm thick, 40mm dia. counter bore of depth „h“ is required.
h = door thickness - 25mm.

Important Notes

Do not activate the latch before closing the door, it may damage the unit.
Other dimensions as per E0300 <X\ E0300#24>. See diagram for mounting dimensions.


| Order No. | Finish | Description | Holding force kg | Weight g |
|--------------|--------------|-------------|---------------------|-------------|
| E0800.AC0030 | Gold | Push Knob | 10 | 93 |
| E0800.AC0040 | Chrome | Push Knob | 10 | 93 |
| E0800.AC0050 | Black Nickel | Push Knob | 10 | 93 |
| E0800.AC0720 | Black | Spacer 2mm | - | 2 |





Push Knobs with latch - for overlay doors

Catches & Latches



E1400

CATCHES & LATCHES

Material

Push button: brass, finished in chrome, satin nickel, satin or polished brass plating.

Push button base: zinc alloy.

Latch body and catch: polyamide.

Technical Notes

Suitable for door thicknesses 19 to 30mm.

Supplied with stainless steel screw (3x16, 3x20).

Important Notes

For correct positioning of push knob from the door surface refer to dimension „x“ on installation diagram.

„x“ is calculated as:

$x = \text{door thickness} + 21,5\text{mm}$


Push knob supplied with two threaded studs of 24mm and 30mm, interchange of stud enables correct positioning of knob to door surface, i.e. dimension „x“.

| Order No. | Finish | Holding force kg | Weight g |
|--------------|----------------|---------------------|-------------|
| E1400.AC0040 | Chrome | 20 | 103 |
| E1400.AC0060 | Satin Nickel | 20 | 103 |
| E1400.AC0070 | Satin Brass | 20 | 103 |
| E1400.AC0080 | Polished Brass | 20 | 103 |





E1600



Material


Body: die cast zinc, chrome plated.
Cylinder lock: die cast zinc, chrome plated.
Lock bolt: die cast zinc.
Supplied with: Keys: two per lock.
Not Supplied: Catch Plate: order separa-

tely.
Technical Notes
Suitable for panel thickness 1-15mm.
When installed lock is, 5mm above surface.

On closing of panel, special contour of the spring loaded cam allows it to be guided over the catch plate, then springs back to lock in place. To open panel, actuate key to release cam, and pull. Cam has stroke of approx, 8mm. Order catch plate separately.

| Order No. | Type | Lock type | Key type | a | b | h grip length |
|--------------|-----------|---------------|-------------|----|---|---------------|
| E1600.AW0010 | Push Lock | Std. Cylinder | Keyed Alike | 29 | 5 | 25 |






Push Lock - Spring Loaded Cam - Push

standard cylinder lock - fixed grip - polycarbonate

Catches & Latches



E1602

CATCHES & LATCHES

Material

Body: polycarbonate, black.

Cylinder Lock: polycarbonate, black.

Supplied With: Keys: two per lock.

Not supplied: Catch plate: order separately.

Technical Notes

Suitable for door thickness 1-16mm.

Tips

On closing of panel, special contour of the spring loaded cam allows it to be guided


over the catch plate, then springs back to lock in place. To open panel, actuate key and depress push button to release cam then pull to open. Optional finger pull can assist in opening (please order separately). Cam has stroke of approx. 8mm.

| Order No. | Type | Lock type | Key type | a | b | h grip length |
|---------------------|-----------|---------------|-------------|----|---|---------------|
| E1602.AW0010 | Push Lock | Std. Cylinder | Keyed Alike | 30 | 4 | 25 |





E1604



Material

Body & insert: die cast zinc, chrome plated.
Cylinder lock: die cast zinc, chrome plated with dust cap.
Supplied With: Keys: two per lock.
Not supplied: Catch plated: order separately.

tely.
Technical Notes
On closing of panel, special contour of the spring loaded cam allows it to be guided over the catch plate, then springs back to


lock in place. To open panel, actuate key to release cam and pull. Cam has stroke of approx. 8 mm. Order catch plate separately.

| Order No. | Actuation | Lock type | Key type | a | b | h grip length |
|--------------|-----------|---------------|-------------|------|---|---------------|
| E1604.AW0010 | Push Lock | Std. Cylinder | Keyed Alike | 22.5 | 5 | 20 |



Push Latch - Spring Loaded Cam zinc

Catches & Latches



E1670

CATCHES & LATCHES

Material

Housing & Button: die cast zinc, nickel plated. IP54 rated.

Technical Notes

Mounted under panel surface so only

button exposed. Mount with 2 x M 3

screws.

Depress button to retract catch and open

panel. Catch has stroke of approx. 7mm.

| Order No. | l_1 | l_2 | l_3 | l_4 | h_1 | h_2 | h_3 | h_4 | w_1 | w_2 | w_3 |
|--------------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| E1670.AW0010 | 30 | 7 | 22 | 10 | 32.6 | 15 | 17.6 | 4 | 12 | 8 | 10 |