





Anti-vibration Impact Plates

metal-rubber

Anti-Vibration



61600

ANTI-VIBRATION

Material

Rubber on silver zinc plated steel (rubber hardness - 60 Shore A).

be drilled to suit the number of threads, thread sizes and the pitch you require.


request.

Technical Notes


The metal plate is provided blank so it can

Part no. 61600.0500-125 has a ribbed base. Other sizes can be supplied on

Order No.	l_1	w_1	h_1	h_2	h_3	Axial load kgf max.	Compression max.
61600.W0035	1250	35	40	30	10	2500	2.0
61600.W0070	180	70	40	30	10	1000	2.8
61600.W0071	245	70	40	30	10	1300	3.7
61600.W0072	285	70	40	30	10	2000	3.6
61600.W0073	320	70	40	30	10	2700	3.5
61600.W0120	250	120	40	28	12	5000	3.3
61600.W0125	500	125	30	15	15	10000	4.0

**61610**

ANTI-VIBRATION

**Material**



Rubber on silver zinc plated steel (rubber hardness - 60 Shore A).

Technical Notes

The metal plate is provided blank so it can be drilled to suit the number of threads,

thread sizes and the pitch you require.
Other sizes can be supplied on request.

Order No.	l_1	w_1	h_1	h_2	Axial load kgf max.
61610.W0060	350	60	40	13	1000
61610.W0061	450	60	40	13	1500
61610.W0062	550	60	40	13	2000



61620

ANTI-VIBRATION

Material

Rubber on silver zinc plated steel (rubber hardness - 60Shore A).

can be drilled to suit the number of threads, thread sizes and the pitch you require. Other sizes can be supplied on request. Suitable for very heavy loads.

Technical Notes

The metal plates are provided blank so they

Order No.	l_1	w_1	h_1	h_2	h_3	Axial load kgf max.
61620.W0040	550	40	40	24	8	2200
61620.W0050	515	50	40	20	10	2800
61620.W0051	515	50	50	30	10	2570
61620.W0060	650	60	50	30	10	3900
61620.W0061	650	60	60	40	10	3500
61620.W0070	600	70	50	30	10	4200
61620.W0171	600	70	55	35	10	4000
61620.W0180	600	80	80	50	15	4320
61620.W0100	415	100	60	30	15	4150
61620.W0101	415	100	80	50	15	3740
61620.W0150	500	150	80	50	15	6750