


Vice Parallels - AccuSnap for use with with AccuSnap master jaws 19810





Material

Body: 80000 psi ductile cast iron.

Technical Notes

Use in conjunction with AccuSnap master

jaws 19810. Parallels snan int

Parallels snap into position quickly and easily. Can be used with AccuSnap modular workstops (except sizes 19812.W0401, W0402, W0601, W0602 and W0801).

Important Notes All dimensions are in inches.


Order No.	Vice size	Ι ₁	h ₁	w ₁
			±0.0005	
19812.W0401	4"	3.98	0.500	0.118
19812.W0402	4"	3.98	0.625	0.118
19812.W0403	4"	3.98	0.750	0.118
19812.W0404	4"	3.98	0.875	0.118
19812.W0405	4"	3.98	1.000	0.118
19812.W0406	4"	3.98	1.125	0.118
19812.W0407	4"	3.98	1.250	0.118
19812.W0408	4"	3.98	1.312	0.118
19812.W0601	6"	5.98	0.750	0.118
19812.W0602	6"	5.98	1.000	0.118
19812.W0603	6"	5.98	1.125	0.118
19812.W0604	6"	5.98	1.250	0.118
19812.W0605	6"	5.98	1.375	0.118
19812.W0606	6"	5.98	1.500	0.118
19812.W0607	6"	5.98	1.625	0.118
19812.W0608	6"	5.98	1.750	0.118
19812.W0609	6"	5.98	1.812	0.118
19812.W0801	8"	7.98	1.000	0.118
19812.W0802	8"	7.98	1.250	0.118
19812.W0803	8"	7.98	1.375	0.118
19812.W0804	8"	7.98	1.500	0.118
19812.W0805	8"	7.98	1.625	0.118
19812.W0806	8"	7.98	1.750	0.118
19812.W0807	8"	7.98	1.875	0.118
19812.W0808	8"	7.98	2.000	0.118
19812.W0809	8"	7.98	2.125	0.118
19812.W0810	8"	7.98	2.250	0.118



Vice Clamping

Vice Parallel Sets - AccuSnap for use with AccuSnap master jaws 19810





Body: 80000 psi ductile cast iron.

Technical Notes

Use in conjunction with AccuSnap master

jaws. Parallels snap into position quickly and easily.

Can be used with AccuSnap modular workstops. Holder racks available see part no. 19838.

Important Notes All dimensions are in inches.

Order No.	Vice size	Туре	Set contents: 1 pair each x dim. h_1 ±0.0005	I_1	w_1
19814.W0040	4"	Basic	0,500 0,750 1,000 1,250 1,312	3.98	0.118
19814.W0060	6"	Basic	0,750 1,000 1,250 1,500 1,750	5.98	0.118
19814.W0080	8"	Basic	1,000 1,250 1,500 1,750 2,000 2,250	7.98	0.118
19814.W0140	4"	Advanced	0,500 0,625 0,750 0,875 1,000 1,125 1,250 1,312	3.98	0.118
19814.W0160	6"	Advanced	0,750 1,000 1,125 1,250 1,375 1,500 1,625 1,750 1,812	5.98	0.118
19814.W0180	8"	Advanced	1,000 1,250 1,375 1,500 1,625 1,750 1,875 2,000 2,125 2,250	7.98	0.118






Vice Mill Angles - AccuSnap

for use with AccuSnap master jaws 19810





Material

Body: 80000 psi ductile cast iron.

Technical Notes

Use in conjunction with AccuSnap master

jaws.

Important Notes All dimensions are in inches.

Order No.	Vice size	Туре	I ₁	h ₁	w ₁	α
19816.W0040	4"	Individual	4	1.240	0.118	20
19816.W0041	4"	Individual	4	1.240	0.118	25
L9816.W0042	4"	Individual	4	1.240	0.118	30
19816.W0043	4"	Individual	4	1.240	0.118	35
.9816.W0044	4"	Individual	4	1.240	0.118	40
9816.W0045	4"	Individual	4	1.240	0.118	45
.9816.W0060	6"	Individual	6	1.174	0.118	20
.9816.W0061	6"	Individual	6	1.174	0.118	25
9816.W0062	6"	Individual	6	1.174	0.118	30
.9816.W0063	6"	Individual	6	1.174	0.118	35
L9816.W0064	6"	Individual	6	1.174	0.118	40
9816.W0065	6"	Individual	6	1.174	0.118	45
9816.W0080	8"	Individual	8	2.230	0.118	20
.9816.W0081	8"	Individual	8	2.230	0.118	25
.9816.W0082	8"	Individual	8	2.230	0.118	30
.9816.W0083	8"	Individual	8	2.230	0.118	35
.9816.W0084	8"	Individual	8	2.230	0.118	40
.9816.W0085	8"	Individual	8	2.230	0.118	45
9816.W0140	4"	Matched Set	4	1.240	0.118	20
9816.W0141	4"	Matched Set	4	1.240	0.118	25
9816.W0142	4"	Matched Set	4	1.240	0.118	30
9816.W0143	4"	Matched Set	4	1.240	0.118	35
.9816.W0144	4"	Matched Set	4	1.240	0.118	40
L9816.W0145	4"	Matched Set	4	1.240	0.118	45
9816.W0160	6"	Matched Set	6	1.174	0.118	20
L9816.W0161	6"	Matched Set	6	1.174	0.118	25
9816.W0162	6"	Matched Set	6	1.174	0.118	30
9816.W0163	6"	Matched Set	6	1.174	0.118	35
9816.W0164	6"	Matched Set	6	1.174	0.118	40
.9816.W0165	6"	Matched Set	6	1.174	0.118	45
L9816.W0180	8"	Matched Set	8	2.230	0.118	20
L9816.W0181	8"	Matched Set	8	2.230	0.118	25
L9816.W0182	8"	Matched Set	8	2.230	0.118	30
L9816.W0183	8"	Matched Set	8	2.230	0.118	35





Vice Mill Angles - AccuSnap for use with AccuSnap master jaws 19810



Order No.	Vice size	Туре	I_1	h ₁	w_1	α
19816.W0184	8"	Matched Set	8	2.230	0.118	40
19816.W0185	8"	Matched Set	8	2.230	0.118	45






Vice Mill Angle Sets - AccuSnap

for use with AccuSnap master jaws 19810





Material

Body: 80000 psi ductile cast iron.

Important Notes All dimensions are in inches.

Technical Notes

For use with our AccuSnap master jaws.

Order No.	For vice size	I_1	h ₁	w_1	Set contents 1 each of a°
19818.W0040	4"	4	1.24	0.118	20° 25° 30° 35° 40° 45°
19818.W0060	6"	6	1.74	0.118	20° 25° 30° 35° 40° 45°
19818.W0080	8"	8	2.23	0.118	20° 25° 30° 35° 40° 45°




Vice Clamping

Machinable Vice Jaws - AccuSnap

for use with AccuSnap master jaws 19810



All dimensions are in inches.



Material

Aluminium or steel.

Technical Notes

For use with our AccuSnap master jaws.

Jaws snap in position quickly and easily.

Important Notes

Sold individually. For a pair please order quantity of 2.

Order No.	For vice size	Material	I_1	h ₁	w ₁
19820.W0040	4"	Aluminium	3.98	1.5	0.690
19820.W0041	4"	Aluminium	3.98	1.5	1.255
19820.W0060	6"	Aluminium	5.98	2.0	0.750
19820.W0061	6"	Aluminium	5.98	2.0	1.500
19820.W0080	8"	Aluminium	7.98	2.5	1.250
19820.W0081	8"	Aluminium	7.98	2.5	2.500
19820.W0140	4"	Steel	3.98	1.5	0.690
19820.W0141	4"	Steel	3.98	1.5	1.255
19820.W0160	6"	Steel	5.98	2.0	0.750
19820.W0161	6"	Steel	5.98	2.0	1.500
19820.W0180	8"	Steel	7.98	2.5	1.250
19820.W0181	8"	Steel	7.98	2.5	2.500






Workstops For Vice - AccuSnap

for use with AccuSnap parallel sets 19812 & 19814





Material

Body: 80000 psi ductile cast iron.

Technical Notes

Ideal for off-line setup. Provides accurate workpiece location and repeatability.

For use with our AccuSnap parallel sets (please order separately).

Important Notes

Install using locating dowel pin into one of three stop locations on face of parallel

(not supplied). Secure workstop by tightening screw. All dimensions are in inches.


Order No.	For vice size	Туре	1		W	\W/
			'1	w ₁	W ₂	W ₃
19830.W0040	4"	Right Hand	1.75	0.469	0.493	0.28
19830.W0041	4"	Right Hand	2.50	0.469	0.493	0.28
19830.W0042	4"	Right Hand	1.75	0.969	0.493	0.28
19830.W0043	4"	Right Hand	2.50	0.969	0.493	0.28
19830.W0060	6"	Right Hand	2.68	0.657	0.493	0.47
19830.W0061	6"	Right Hand	3.68	0.657	0.493	0.47
19830.W0062	6"	Right Hand	2.68	1.157	0.493	0.47
19830.W0063	6"	Right Hand	3.68	1.157	0.493	0.47
19830.W0080	8"	Right Hand	3.50	0.626	0.618	0.44
19830.W0081	8"	Right Hand	5.00	0.626	0.618	0.44
19830.W0082	8"	Right Hand	3.50	1.126	0.618	0.44
19830.W0083	8"	Right Hand	5.00	1.126	0.618	0.44
19830.W0140	4"	Left Hand	1.75	0.469	0.493	0.28
19830.W0141	4"	Left Hand	2.50	0.469	0.493	0.28
19830.W0142	4"	Left Hand	1.75	0.969	0.493	0.28
19830.W0143	4"	Left Hand	2.50	0.969	0.493	0.28
19830.W0160	6"	Left Hand	2.68	0.657	0.493	0.47
19830.W0161	6"	Left Hand	3.68	0.657	0.493	0.47
19830.W0162	6"	Left Hand	2.68	1.157	0.493	0.47
19830.W0163	6"	Left Hand	3.68	1.157	0.493	0.47
19830.W0180	8"	Left Hand	3.50	0.626	0.618	0.44
19830.W0181	8"	Left Hand	5.00	0.626	0.618	0.44
19830.W0182	8"	Left Hand	3.50	1.126	0.618	0.44
19830.W0183	8"	Left Hand	5.00	1.126	0.618	0.44



Spacers - AccuSnap

for use with AccuSnap workstop 19830





Material

Body: 80000 psi ductile cast iron.

Vice Clamping

Technical Notes

For use with AccuSnap workstop no. 19830,

spaces enables workstop to be offset from parallel face. For use with our AccuSnap workstop and parallel sets (please order separately).

Important Notes

All dimensions are in inches.

Order No.	For vice size	w_1
19832.W0040	4"	0.375
19832.W0060	6"	0.375
19832.W0080	8"	0.500






AccuSnap Jaws and Parallels

for use on SnapLock Jaw System for ReLock Vices

19810 - 19838 Clamping & Height Setting

- Fast, accurate and versatile.
- Reduces setup time drastically.
- ±0,0002" repeatability.
- Adaptable to most vice systems.






Before mounting AccuSnap master jaws, thoroughly inspect, clean and remove any burrs or chips from the mounting surface. **VICE CLAMPING**

Simply attach the AccuSnap master jaws to the carrier jaw system using the industry standard bolt system.



Step 2:

Snap in the parallels or soft jaws that you require for your set-up and begin machining. Two lock screws are provided for extra holding assurance, but are not necessary to hold parallels in place. Do not overtighten lock screws.



Step 3:

When finished with your job, unlock parallels (if needed) and turn the kick out screw to eject the jaw or parallel. You are ready to repeat the process for your next job.

0333 207 4497

SnapLock[®], AccuSnap[®], QuickChange[™]

interchangeable jaws, parallels and mill angles



ReLock Accessories

Both the AccuSnap and QuickChange vice jaw systems can be used in conjunction with most vice systems.



SnapLock Machinable Fixture Jaws

Jaws can be attached, reversed, removed or indexed in a matter of seconds. The jaws are extremely versatile, allowing endless customising possibilities. Jaws are manufactured from steel and high quality aluminium.



SnapLock Carrier Jaws

Carrier jaws allow mounting of AccuSnap and QuickChange master jaws or standard bolt-on jaws using an industry standard bolt pattern.



QuickChange Vice System

QuickChange jaws slide into position via a dovetail slot, as shown. The system includes master jaws, parallels, V-blocks, mill angles and machinable soft jaws. Adaptable to most vice systems.



AccuSnap Vice Jaw System

The AccuSnap vice jaw system (pictured), shows master jaws and parallels being used for workpiece set-up. The AccuSnap system allows setup change-over in seconds with extreme accuracy.



AccuSnap Machinable Fixture Jaws Ideal for many workholding options of smaller workpieces. Jaws are offered in two thicknesses, from either aluminium or pre-hardened steel.

wixroyd.com



AccuSnap Workstops

Easily mount to AccuSnap parallels in a variety of configurations. Provides extreme workpiece location accuracy and repeatability. Can be used in conjunction with the AccuSnap presetting gauge to accurately reference your X, Y and Z machine datums.





How to use the SnapLock Jaw System

19790-19862 Clamping & Height Setting

The SnapLock system's allows simple, quick changeovers between machinable and carrier jaws.

SnapLock Machinable Fixture Jaws


- Can be attached, reversed, removed or indexed in a matter of seconds.
- Extremely versatile, allowing endless customisation possibilities.
- Manufactured from high quality aluminium.

Operation

SnapLock Carrier Jaws


 Allows mounting of AccuSnap and QuickChange master jaws or standard bolt-on jaws using an industry standard bolt size and pattern.





Step 1

Align the SnapLock outer jaw over the appropriate ReLock vice knuckle




Step 2

Place the front edge of the jaw over the knuckle and press firmly down to "snap" into place

Step 4

For jaw removal, simply unbolt the centre jaw and slip pry wrench in slots of outside jaws as shown; pull back or sideways on the handle to release

0





0333 207 4497

sales@wixroyd.com





Foundation


The ReLock vice is the foundation for a fully flexible vice system, with a multitude of interchangeable jaws, parallels or mill angles to suit your application.

Base vice - ReLock 2 or ReLock 8.

- SnapLock[®] Carrier Jaws accepts both AccuSnap[®] and QuickChange[™] Jaw systems.
- AccuSnap or QuickChange Parallels and Mill Angles select the approach best suited to your application.

VICE CLAMPINO

Flexibility



1 SnapLock Carrier Jaws

SnapLock carrier jaws allow mounting of AccuSnap and QuickChange master jaws by using an industry standard bolt size and pattern. Carrier jaws snap on and off the SnapLock knuckles in seconds.

(2) (3) AccuSnap and QuickChange Master Jaws

AccuSnap QuickChange master jaws easily mount to the SnapLock carrier jaws by using an industry bolt size and pattern. AccuSnap master jaws patented locking receptacle accepts all AccuSnap accessories.

4 5 AccuSnap and QuickChange Parallels

AccuSnap and QuickChange parallels are designed for a range of set up variations when you need to position a workpiece between hardened jaws. AccuSnap parallels snap in and out of the AccuSnap master jaws in seconds. QuickChange parallels slide into position via a dovetail slot and gib.

Also available:

Machinable Fixture Jaws

AccuSnap and QuickChange machinable fixture jaws can be customised quickly to fixture a wide range of workpieces. The jaws snap or slide in and out of the master jaws in seconds. Available in either aluminium or hardened steel.

SnapLock Reversible Machinable Fixture Jaws

SnapLock reversible machinable fixture jaws are the most versatile method of fixturing on the ReLock System. Customising options are endless. Jaws can be machined on two faces for additional set up. Manufactured from high quality aluminium.

Fixture Plate

Ideal for a wide variety of fixturing applications, such as holding many small parts or parts with difficult clamping or locating requirements. Fixture plates can be attached or removed in seconds and are offered in two widths. Manufactured from high quality aluminium.

Modular Workstops

AccuSnap modular workstops quickly mount to parallels in many different positions. As many as three stops can be mounted to a single parallel to accommodate multi-piece set-ups.

Universal Workstop

The universal workstop easily mounts to the side of the ReLock in numerous positions. Optional extension is available for larger workpieces.

Workstop Presetting Gauge

The AccuSnap workstop presetting gauge, in combination with a standard micrometer, allows you to precisely preset your modular workstop positions in relation to the X, Y, and Z machine datums.

Single Station Conversion Plate

The single station conversion plate quickly converts the ReLock from double station to single station vice for larger workpieces.





ReLock Modular Workholding






Optimised Table Space

Compact modular design allows a multitude of mounting configurations. Vices can be mounted close together without hindering the removal or attachment of jaws. The ReLock 8-station (shown) is ideal for horizontal machining centres, as well as for use with rotary indexers on vertical machining centres.




Locating and Mounting

Locating and mounting options are simple and accurate. The bottom surface of the system has four precision dowel pin holes for locating and four drilled and counterbored holes drilled through from the top surface for rugged mounting. Side clamp slots are also incorporated.



ReLock Chip Shields

ReLock's unique three piece telescopic chip shield wraps completely around the SnapLock knuckles, keeping swarf from getting into the vice's clamping mechanism. Shields can be quickly and easily removed for maintenance purposes.



Single Station Conversion


Used in conjunction with SnapLock carrier jaws, the conversion plate allows the ReLock system to be converted from a double to a single station vice - ideal for larger workpieces.



Centre Jaw Location

ov-W19768-A-T-relock-modular-work-holding-rnh - Updated -25-10-2022

The ReLock's centre jaw locating studs allow quick jaw mounting and indexing to accuracies of ±0.0005". Foolproof pin eliminates the possibility of the jaws being accidentally mounted in reverse.



SnapLock Knuckle Exclusive SnapLock knuckle allows SnapLock soft jaws and SoftLock carrier to be attached and removed in seconds.





0333 207 4497

Auto Offset Mechanism

non-simultaneous workpiece clamping and unclamping to one of the three optional offset settings: 4" and 6": 0.030", 0.125", or 0.250"; 8": 0.125", 0.250", or 0.375". The offset setting is the distance the rear jaw backs away from the workpiece before the front jaw begins to back away from the workpiece.

sales@wixroyd.com

Exclusive automatic offset mechanism allows