


## **CMM Fixturing Plastic Sets**

# **Gauging** & Inspection



#### Material

Clamps, rest feet: nylon 101. Studs, coupling nuts and washers: steel. Supplied in metal tray for improved organi-

#### sation.

Tips Lightweight components reduce risk of

Thread size Studs Order No. Nylon clamps Extension nuts Nylon star knob Support feet Nylon washers Weight g 50mm x 4pcs 75mm x 4pcs 63mm x 4pcs 19370.W0008 Μ8 100mm x 4pcs 90mm x 4pcs M 8 x 4pcs M 8 x 4pcs M 8 x 4pcs for M 8 x 8pcs 2495 125mm x 4pcs 150mm x 4pcs 115mm x 4pcs 50mm x 4pcs 75mm x 4pcs 63mm x 4pcs 19370.W0010 M10 100mm x 4pcs 100mm x 4pcs M10 x 4pcs M10 x 4pcs M10 x 4pcs for M10 x 8pcs 2857 125mm x 4pcs 150mm x 4pcs 150mm x 4pcs 50mm x 4pcs 75mm x 4pcs 63mm x 4pcs 19370.W0012 M12 100mm x 4pcs 100mm x 4pcs M12 x 4pcs M12 x 4pcs M12 x 4pcs for M12 x 8pcs 4991 125mm x 4pcs 150mm x 4pcs 150mm x 4pcs



damage to the CMM table.







Wixroyd's CMM fixturing system is designed for easy assembly and high repeatability, eliminating the need to build dedicated fixtures. The system offers a highly accurate and flexible solution of holding parts while probing on CMMs.

### Flexible

A variety of component parts as well as complete kits are available; to enable setup of fixtures in minutes.







- Aluminium base plates hole based system with alpha-numeric labelling for easy set-up and recording of fixture positions.
- Fixture towers ideal for fixturing of large vertical components.
- Soft-touch clamps non-marking clamps providing the ideal force for holding parts during CMM probing.
- Locating components rest pads, vee pads for cylindrical parts, pin rests etc.

